



MCH heater system, 15' start to work  
450F keratin treatment straightener iron  
Nano silver ceramic coating



Pivoting Swivel power cord

Advanced Ceramic Coating plates  
Extra long & Floating plate(110 x 24mm)



Up to 230°C (450F)  
LCD temperature display

□□□ □□ □□ □□□□:



Blister inner tray

□□□ □□ EMS-7118 □□ □□□□:

- \* [00\\_00\\_0000\\_00\\_00](#);
- \* 00000 000, 00 0000, 00 000 00;
- \* MCH 00 000, 40 200 c;
- \* 00 00 00 0 0 00;
- \* LCD 00 230 c; 150 C00 000 00
- \* 00 360 00 00 00, convinient 0 00 00 0 000;
- \* 000 0 9 0 00 000; 00 00 000 0 0 00
- \* 000 GHD styler affordable 00 0 00 00;
- \* 00, 0000 000000 00 00 0000 00 00.



**00 000 00:**

<p>0000 00 00:</p>	<ul style="list-style-type: none"> <li>* 00 00 000</li> <li>* GB 00: 37 * 10 * 5.3cm</li> <li>* 20pcs/CTN</li> <li>* 0 0 00: 56.5 * 38.5 * 24 cm</li> <li>* G.W.: 15.0KGS</li> <li>* 0000 0 0: 9.0KGS</li> <li>* 1 * 20GP: 11, 000pcs</li> <li>* 1 * 40GP: 21, 000pcs</li> </ul>
<p>00000:</p>	<p>000000 00 00</p>

**0000 00 00 00:**

- 0000 000, 00 0 00000. [0000\\_00\\_000000\\_00\\_0\\_0\\_00](#), [00\\_00\\_00\\_0\\_00\\_00](#).
- 1 00: 00 0000 00 00 0000 0000 00 0 0 0000 00 00 0 0 00 00 00 000000 0000.
  - 2 00: 00 0 00 00, 0 000 Spary 00 0 00 0000 0000.
  - 3 00: straighteing 0000 00 00 0000 00 00 00 00 00000.
  - 4 00: 0000 0000 0000
    - 1) 00 00 00 0 0 0000 0 0 0000. 000000 00 0 00; 0 00 00 0 0 30 0 0000
    - 2) 0000 0000 00 0 0 0, 00 00 0000 00 00 00000 0000 0 00000 0000 00 0 0 00000 0000.
- 00 00 00 0 0000 0000 00000 00 0000 3) 00 00 0000 0000 0000 0000.



**air**

FBT [GHD](#) 2 straighteners.

